







FEMALE END VIEW	TYPICAL BOARD LAYOUT	PIN DETAIL A	SPECIFICATIONS	
			CONTACT CARRIER MATERIAL/COLOR	NYLON OR TPU/BLACK
			CONTACT MATERIAL/PLATING	BRASS/GOLD
			RATED CURRENT [A]	4.0 A
			RATED VOLTAGE [V]	60 VAC/75VDC
			TEMPERATURE RANGE	-30°C to +80°C (-22°F to +176°F)



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<div style="display: flex; justify-content: space-between;"> <div data-bbox="1480 1307 1848 1372"> <b>TURCK INC</b>  <i>High Technology Sensors and Automation Controls</i> </div> <div data-bbox="1869 1291 2058 1396">           3000 CAMPUS DRIVE            MINNEAPOLIS, MN 55441            1-800-544-7769            (763) 553-7300            (763) 553-0708 fax            turck.com         </div> </div>	
MATERIAL  SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT JBU DATE 04/28/99	DESCRIPTION MFKB 3 (10/BAG)	
FINISH  SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b> DO NOT SCALE THIS DRAWING		IDENTIFICATION NO. E1123 REV C FILE: E1123 SHEET 1 OF 1

C DRAWING PROCESSED AS PART OF ECO 33971	CBM 04/07/11	33971
REV DESCRIPTION	BY DATE	ECO NO.