



Zeichnung	Amp.	16	32
1 MB 256	Pole	7	7
Maße in mm	a	100	100
	b	92	92
	c	48	51
	d	85	85
	d.1	42,5	45,5
	e	77	77
	f	5,1	5,1
	g.	6	6
	g.1	2	2
	h	100	102
	k	39	58
	l	78	78
	l.1	78	87
Leiterquerschnitt		1,5	2,5
von bis mm ²		—4	—10