

## Datasheet

# RS Pro Non-Fused Terminal Block, 5 Way/Pole, 4 mm<sup>2</sup>, Nylon, 450 V

RS Stock No: **469-1824**



## Product Details

RS Pro non-fused terminal block is suitable for use with circular profile cables for indoors or outdoors. This versatile cable connector is IP68 rated, it means it can be used underwater or underground. The internal terminal block is easily accessible and quickly wired. This 5-way block comes with metal mounting clip. The block has 2-part gland body sealing ring that allows the use of a wide cable diameter range. This terminal block with 4 mm<sup>2</sup>, is made of nylon material. The block with 450 V voltage rating, has brass contact with nickel plating.

## Features and Benefits

- Tested to IP68 at 5 bar
- Temperature range from -20 to +125°C
- Rated at 450 V/32 A
- Barrel in nylon 66 with cable gland and terminal block in nylon
- 115 mm (3-pole), 130 mm (5-pole) long
- Diameters 26.5 mm and 32 mm respectively
- Cable gland size M20 (3-pole), M25 (5-pole)

**Specifications:**

Contact Material	Brass
Contact Plating	Nickel
Current Rating	32 A
Enclosed	Yes
Material	Nylon
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-40°C
Number of Ways	5
Voltage Rating	450 V
Wire Size	4 mm <sup>2</sup>
Colour	Grey
Standards Met	RoHS Compliant