




| LOC |     | DIST        |  | REVISIONS |           |      |      |  |
|-----|-----|-------------|--|-----------|-----------|------|------|--|
| J   |     | -           |  | 変更        |           |      |      |  |
| P   | LTR | DESCRIPTION |  |           | DATE      | DWN  | APVD |  |
|     | A   | RELEASED    |  |           | 18AUG2006 | J. A | D. M |  |
|     | B   | REVISED     |  |           | 05DEC2008 | T. S | A. O |  |
|     |     |             |  |           |           |      |      |  |
|     |     |             |  |           |           |      |      |  |


- 1: AS SHOWN



CONTACT 6  
CONTACT 3  
CONTACT 2  
CONTACT 1



RECOMMENDED STRIPPING LENGTH



1. MATERIAL : CASE HOUSING-POLYCARBONATE.  
TERMINAL HOUSING-NYLON.  
CONTACT-COPPER ALLOY.  
SHELL-COPPER ALLOY.  
2. FINISH : CONTACT-UNDERPLATE: Ni  
CONTACT AREA: Au  
SHELL: Ni

COLOR ALLOCATION OF TERMINAL WIRE TO RJ45 CONTACT

| CONTACT NO. | WIRE COLOR |
|-------------|------------|
| 1           | YELLOW     |
| 2           | ORANGE     |
| 3           | WHITE      |
| 6           | BLUE       |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:  
単位: 概  
mm

MATERIAL  
材料

-

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

一般公差 ± 0.3

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ± 3

FINISH  
仕上

-

DWN  
J. AKASAKA  
29NOV2005

CHK  
D. MITSUGI  
IDEC2005

APVD  
D. MITSUGI  
IDEC2005

PRODUCT SPEC  
108-78381

APPLICATION SPEC  
取付適用規格  
114-5402

WEIGHT  
-

CUSTOMER DRAWING

WIRE RANGE  
絶縁電線断面積  
-

INSULATION DIA  
被覆外径  
φ 6.5

Tyco Electronics AMP K.K.  
Kawasaki, Japan

NAME  
名称

RJ 45 CONNECTOR  
INDUSTRIAL ETHERNET  
IP20 4POS 180DEG

SIZE  
A3

CAGE CODE  
-

DRAWING NO  
番号  
C-1903526

RESTRICTED TO  
-

SCALE  
尺度  
2:1

SHEET  
1

OF  
1

REV  
B