

## • PA-1000B 30W Amplifier

### Features:

- Output Power - 30W/100V line/4 /8
- Inputs:
  - 3 Inputs - MIC1, MIC2, AUX & Telephone Input
  - MIC Inputs have both XLR and 1/4" Jacks
- Muting for Priority:
  - Input MIC1 has automatic priority over MIC2 and AUX (defeatable)
  - Telephone Input has automatic priority over all other inputs
- Remote Chime activation



### Specifications:

Model:	PA-1000B:
Rated Power Output (THD 1%)	30W
Output Level/Impedance (Transformer)	100V/333 , 15V/8 , 11V/4
Pre-Amp Output	1V/600
Input Sensitivity/Impedance:	MIC 1, 2 Jack 1mV/600 XLR 0.3mV/600 AUX Amp In 100mV/10K IV/10K Telephone In 0.775V/600
Frequency Response	80Hz ~ 15KHz
Tone Control:	Treble (10KHz) ± 10dB Bass (100KHz) ± 10dB
Power Source	AC 230V 50Hz
Dimensions	300(W) x 88(H) x 260(D) mm
Weight	4.6kg

