

General Information

Extended Product Type:	332BS6
Product ID:	2CMA193322R1000
EAN:	7392696933223
Catalog Description:	Surface inlet, 6h, 32A, IP44, 3P+E
Long Description:	Surface Inlet, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Inlets

Ordering

EAN:	7392696933223
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	85 mm
Product Net Height:	153 mm
Product Net Length:	94 mm
Product Net Depth:	153 mm
Product Net Weight:	0.27 kg

Container Information

Package Level 1 Width:	179 mm
Package Level 1 Length:	430 mm
Package Level 1 Height:	193 mm
Package Level 1 Gross Weight:	0.35 kg
Package Level 1 EAN:	7392696933223
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Cable Cross-Section:	2.5 ... 10 mm ²
Color:	Red
Degree of Protection:	IP44
Enclosure Material:	Thermoplastic
Frequency (f):	60 Hz
Function:	Surface inlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#332BS6
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	EBS
Product Name:	Industrial Surface Inlet
Protection Type:	Splashproof
Rated Current (I _n):	32 A
Rated Voltage (U _r):	380 ... 415 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Surface Inlets
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2417186

UNSPSC: 39120000

