


44 21 J11

Circlip Pliers for internal circlips in bore holes



- Solid style, forged
- Non-slip, solid tips
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened
 - Style: DIN 5256 D; 90° angled tips



| | |
|-----------------------------|--------------------|
| Article No. | 44 21 J11 |
| EAN | 4003773011194 |
| Pliers | black atramentized |
| Head | polished |
| Handles | plastic coated |
| Style | 2 |
| Size of bore Ø mm | 12 - 25 |
| Style | bent tips |
| Ø mm | 12 - 25 |
| Tips (diameter) Ø mm | 1,3 |
| Length mm | 130 |
| Net weight g | 88 |

technical change and errors excepted

