

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

-

A

ECN EH10 0344 05




09 MAR 05

MG

MG



OPTIONAL

"L" MAX.

2,5
[0,098]

A

POS 1

SECTION A-A
SCALE 10:1SECTION B-B
SCALE 10:1

PARTNUMBER	POS	"L" MAX	
		MM	INCH
0-5164713-3	3	7.5	.295
0-5164713-4	4	10.0	.394
0-5164713-5	5	12.5	.492
0-5164713-6	6	15.0	.591
0-5164713-7	7	17.5	.689
0-5164713-8	8	20.0	.787
0-5164713-9	9	22.5	.886
1-5164713-0	10	25.0	.984
1-5164713-1	11	27.5	1.083
1-5164713-2	12	30.0	1.181
1-5164713-3	13	32.5	1.280
1-5164713-4	14	35.0	1.378
1-5164713-5	15	37.5	1.476
1-5164713-6	16	40.0	1.575
1-5164713-7	17	42.5	1.673
1-5164713-8	18	45.0	1.772
1-5164713-9	19	47.5	1.870
2-5164713-0	20	50.0	1.969

2	CONTACT	BRASS	TIN OVER NICKEL
1	HOUSING	PBT 20% GF, COLOR GREEN	
ITEM NO.	DESCRIPTION	MATERIAL	FINISH
DWN	09 MAR 05		
CHK	M. GOSSELINK		
APVD	M. GOSSELINK		
PRODUCT SPEC			
APPLICATION SPEC			
WEIGHT			
CUSTOMER DRAWING			
SCALE	5:1	SHEET	1 OF 1
REV	A		

tyco
ElectronicsTYCO ELECTRONICS NEDERLAND B.V.
's-HERTOGENBOSCH, THE NETHERLANDSNAME
MINI-MATCH CONNECTOR ASS'Y
3-20 POS 2.5 MM PITCH

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=5164713