

NS750 LED & LED LITE







- High performance rechargeable LED utility searchlight
- 1000 metre beam
- 1500 | 1000 lumens
- 4 modes: high, low, flashing, strobe
- 5° optics for long distance and even beam spread
- Supplied with a mains charger
- Battery charging indicator (red to green)

Two optional battery choices




NS750 LED AND LED LITE

This is the LED version of the NIGHTSEARCHER NS750 designed in conjunction with UK Power Networks. However, it is also ideal for inspection tasks across all sectors. Using 9 powerful Cree® LEDs, a light output of 1500 lumens is achieved on high, along with a 1000 metre beam. The LEDs now ensure a much longer running time, enough to cover an 8 hour shift.

Two optional battery choices	NS750 LED			NS750 LED LITE		
	 5h 10h30	 3.1Kg		 8h 14h	 1.7Kg	
Run time	5h 10h30			8h 14h		
Battery	12V 7Ah SLA			14.8V 7.8Ah Li-ion		
Product weight (kg)	3.1			1.7		
Boxed weight (kg)	3.8			2.2		
Part No.	NS750LED			NS750LEDLITE		
CAT/PAD No.	Coming soon			Coming soon		

NS750 LED / NS750 LED LITE	
Charge time	8h
Product size (mm)	L250 x W115x H280
Boxed size (mm)	L269 x W224 x H204

