



ENGLISH

Datasheet

Stock No: 191-6754

# RS Pro M50 Black Nylon Cable Gland With Locknut, 36.5 → 43mm Cable Dia Range, IP68



## Product Details

### IP68 Metric Nylon A2P Gland

UV resistant compression glands with nitrile seals. Protection rating of IP68. Seal rotation is prevented by a reduced friction skid washer incorporating an air cushion. Supplied complete with locknut and sealing washer. May be used as a replacement for A2 metal glands.

Temperature Rating	-10 → 90°C
Colour	Black
Thread length	11mm



ENGLISH

## Specifications:

Thread Size	M50
Material	Nylon 66
Maximum Cable Diameter	43mm
Minimum Cable Diameter	36.5mm
Colour	Black
IP Rating	IP68
Minimum Operating Temperature	-10°C
Maximum Operating Temperature	+90°C