

BC190 Line Voltage Adapter / Battery Charger

[Product Home](#)

Provides power cord operation and charging for ScopeMeter 190 Series test tool.

Mains (Line Voltage):

BC190/801 (Europe) 230V $\hat{A} \pm 10\%$

BC190/803 (North America) 120V $\hat{A} \pm 10\%$

BC190/804 (United Kingdom) 230V $\hat{A} \pm 10\%$

BC190/806 (Japan) 100V $\hat{A} \pm 10\%$

BC190/807 (Australia) 230V $\hat{A} \pm 10\%$

BC190/808 (Universal) switchable 115V $\hat{A} \pm 15\%$ or 230V $\hat{A} \pm 15\%$

/808 are equipped with a male receptacle plug that must be connected to a line cord appropriate for local use.

(Line cord not included)

- **Frequency (all versions):** 50-60Hz $\hat{A} \pm 10\%$
- **Output Voltage:** 17.8V DC
- **Output Power:** 15W
- **Power Consumption:** 23.7VA
- **Max. Voltage to Ground:** 600V rms. CAT III per IEC 1010-