




LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			N1	REVISED PER ECO-11-004587	11MAR11	RK	HMR



- 1 MATES WITH .032±.001x.250 TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .260 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA
- 7 PRELIMINARY - NOT FOR PRODUCTION



STANDARD	HOUSING:NYLON,COLOR-BLACK RECEPTACLE:#3 HARD BRASS,TIN .000080 MIN	9-520140-2
BULK	HOUSING:NYLON,COLOR-BLUE TRANSLUCENT RECEPTACLE:#3 HARD BRASS,TIN .000080 MIN	5-520140-2
STANDARD	HOUSING:NYLON,COLOR-BLUE TRANSLUCENT RECEPTACLE:#3 HARD PH BRONZE,TIN .000080 MIN	3-520140-4
STANDARD	HOUSING:NYLON,COLOR-BLUE TRANSLUCENT RECEPTACLE:#3 HARD BRASS,TIN .000080 MIN	3-520140-2
PACKAGING	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 21NOV00		 TE Connectivity					
DIMENSIONS: INCHES			CHK MS FEHER 21NOV00							
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSY, ULTRA-FAST, .250 SERIES, 16-14 AWG					
			0 PLC ± -							
			1 PLC ± -							
			2 PLC ± -							
			3 PLC ± -.015							
MATERIAL SEE TABLE			4 PLC ± -		SIZE A2					
			ANGLES ± ±					CAGE CODE 00779		
			FINISH							
SEE TABLE			SEE TABLE		RESTRICTED TO -					
			PRODUCT SPEC 108-2043		SCALE 4:1					
			APPLICATION SPEC 114-2123					SHEET 1 of 1		
			WEIGHT -		REV N1					
			CUSTOMER DRAWING							