

Inline terminal - IB IL 24 PWR IN/M - 2861027

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Inline power terminal without fuse in acc. with the requirements of Germanic Lloyd (GL)

Why buy this product

- Supply of the 24 V main voltage UM
- Provision of the 24 V segment voltage US
- Station protected against conducted surge voltages
- Option to tap the protected 24 V voltage, to provide bus terminal supply UBK
- Diagnostic and status indicators



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 904654
Weight per Piece (excluding packing)	51.39 g
Custom tariff number	85389091
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Interfaces

Connection method	Inline data jumper
Interface	Inline local bus

Inline terminal - IB IL 24 PWR IN/M - 2861027

Classifications

eCl@ss

eCl@ss 4.0	27250308
eCl@ss 4.1	27250304
eCl@ss 5.0	27250304
eCl@ss 5.1	27242610
eCl@ss 6.0	27242610
eCl@ss 7.0	27242610
eCl@ss 8.0	27242610

ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001600
ETIM 4.0	EC001600
ETIM 5.0	EC001600

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals


Approvals

UL Recognized / cUL Recognized / LR / GL / BV / DNV / ABS / RINA / GL-SW / GL-SW / BSH / GL / cULus Recognized / GL

Ex Approvals

Approvals submitted

Approval details

UL Recognized 

Inline terminal - IB IL 24 PWR IN/M - 2861027

Approvals

cUL Recognized

LR

GL	
mm ² /AWG/kcmil	6

BV

DNV

ABS

RINA

GL-SW	
mm ² /AWG/kcmil	6

GL-SW	
mm ² /AWG/kcmil	6

BSH

GL	
mm ² /AWG/kcmil	6

cULus Recognized

GL

Inline terminal - IB IL 24 PWR IN/M - 2861027

Accessories

Accessories

Labeling panel

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Plug

Inline connector - IB IL SCN-PWR IN-CP - 2727637



Connector, colored, for Inline power and segment terminal blocks

Inline connector - IB IL SCN-PWR IN - 2727462



Connector, for Inline power and segment terminal blocks

Terminal marking

Insert strip - ESL 62X10 - 0809492

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Plotter: Laser printer, Mounting type: Insert, Lettering field: 62 x 10 mm

