






RECOMMENDED MOUNTING:

M4 FASTENER WITH 6.00 IN-LB [7.00 KGF-CM] OF TORQUE MAX.


CHARACTERISTICS

ELECTRICAL RATING	15A 125VAC OR 250VAC UL APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	350 GMS
RELEASE FORCE MIN.	114 GMS
PRETRAVEL MAX.	.016 [0.4 mm]
OVERTRAVEL MIN.	.140 [3.58 mm]
MOVE. DIFF. MAX.	.002 [0.05 mm]
OPERATING POSITION	1.268 TO 1.362 [32.2 TO 34.6 mm]

DWN: JED
APVD: SB
DATE: 25-May-04
THIRD ANGLE PROJECTION

THE CONFIDENTIAL AND PROPRIETARY
INFORMATION CONTAINED IN THIS DOCUMENT
IS OWNED BY CHERY ELECTRICAL PRODUCTS.
A DIVISION OF THE CHERY CORPORATION WHO
MUST GIVE WRITTEN PERMISSION BEFORE THE
DOCUMENT OR INFORMATION CAN BE COPIED,
DISCLOSED OR USED IN ANY WAY.

CHERRY
ELECTRICAL PRODUCTS
11220 80TH AVENUE
PLEASANT PRAIRIE, WI 53159



TOLERANCE UNLESS SPECIFIED

X.XX	X.XXX	ANGLES
± 0.02	± 0.015	± 5.0°

SWITCH
C ITEM NO. GPTCRH01

REV	PCN NO	DATE	PRP	APVR
C	12934	01-Jun-05	JED	SG

PROJECT / 154

SCALE: 2-1 SH 1 OF 1

ORIGINAL ON PROVE