

ML Home

ML HOME 11W E27 827 SLV

0035002

Range features



PRODUCT OVERVIEW

Ordering number	0035002
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	8,000
Lamp shape	Stick
Lamp finish	Frosted
Dimmable	No
Cap/Base	E27
Type	STICK
EAN code	5410288350028
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	560
Efficacy (Rated) (lm/w)	48
Watt (Nominal) (W)	11
Equivalent watt (W)	48
Voltage (V)	220-240

ML Home

ML HOME 11W E27 827 SLV

0035002

DATA TABLE

General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035002
Energy saving lamp	Yes
Average life (Rated) (h)	8,000
Energy class	A
Average life (Nominal) (h)	8000
Lamp finish	Frosted
Lamp shape	Stick
Dimmable	No
Cap/Base	E27
Type	STICK
EAN code	5410288350028
E-number FI	4940269
E-number SE	8357521
Long description	
Product name	ML HOME 11W E27 827 SLV
Lamp mercury content (mg)	<2.0mg
Starting time (max) (s)	<1sec
Warm-up time to 60% of full light (max) (s)	<40sec
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	=30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	560
Lumen maintenance at end of nominal life (%)	=70%
Luminous flux (Nominal) (lm)	560

ML Home

ML HOME 11W E27 827 SLV

0035002

Electrical data

kWh per 1000 hours burning time	11
Efficacy (Rated) (lm/w)	48
Watt (Rated) (W)	11
Watt (Nominal) (W)	11
Equivalent watt (W)	48
Voltage (V)	220-240
Lamp power factor	0.55

Physical data


Weight (kg)	0.05
Lamp Length (mm) - C/L	120
Max. Lamp Diameter (mm) - D	42
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	12.80 x 4.40 x 4.20
Outer package dimensions (L x W x H) (cm)	23.50 x 9.50 x 14.30

ML Home

ML HOME 11W E27 827 SLV

0035002

TECHNICAL DRAWINGS



ENERGY LABEL

