

Thrust ball bearings, single direction

Principal dimensions				Basic load ratings		Speed ratings		Designations	
d	D	H	H1	dynamic C	static C0	Reference speed	Limiting speed	Bearing	Seat washer
mm				kN		r/min		-	-
17	30	9	-	11,4	21,2	8500	12000	51103	-

