

GROUP 230 CUTTING & GRINDING DISCS

NORTON Depressed Centre Reinforced Cutting & Grinding Discs

A range of discs for all angle-grinding of both metal (aluminium oxide) and stone (silicon carbide).

Reinforced Depressed Centre Cutting & Grinding Discs



Size (mm)	Grade	Form	Order Code NOR-230	List Price/1	Offer Price/1
115 x 1.0 x 22.2	Metal/Inox	Flat	-2114C	£1.93	£1.45
115 x 1.6 x 22.2	Metal/Inox	Flat	-2114W	£1.55	£1.16
115 x 2.0 x 22.2	Metal/Inox	Flat	-2115A	£1.65	£1.24
230 x 2.0 x 22.2	Metal/Inox	Flat	-2270S	£4.03	£3.02
230 x 2.5 x 22.2	Metal/Inox	Flat	-2276M	£4.22	£3.17
100 x 2.5 x 16	Metal/Inox	DPC	-2104K	£1.92	£1.44
115 x 2.5 x 22.2	Metal/Inox	DPC	-2115D	£1.80	£1.35
115 x 3.2 x 22.2	Metal/Inox	DPC	-2121S	£2.95	£2.21
125 x 2.5 x 22.2	Metal/Inox	DPC	-2160A	£1.84	£1.38
125 x 3.2 x 22.2	Metal/Inox	DPC	-2166G	£1.60	£1.20
180 x 2.5 x 22.2	Metal/Inox	DPC	-2200A	£3.14	£2.36
230 x 2.5 x 22.2	Metal/Inox	DPC	-2280V	£4.05	£3.04
230 x 3.2 x 22.2	Metal/Inox	DPC	-2340K	£2.66	£2.00
230 x 3.2 x 22.2	Stone	DPC	-2341L	£2.83	£2.12
100 x 6.5 x 16	Metal/Inox	DPG	-2112S	£2.68	£2.01
115 x 6.5 x 22.2	Metal/Inox	DPG	-2130G	£2.76	£2.07
125 x 6.5 x 22.2	Metal/Inox	DPG	-2170M	£2.95	£2.21
230 x 6.5 x 22.2	Metal/Inox	DPG	-2360S	£6.94	£5.21
115 x 7.0 x 22.2	Metal/Inox	DPC	-2140P	£5.42	£4.07

3M Green Corps™ Cut-Off Wheels

These revolutionary cut-off wheels last up to eight times longer than conventional aluminium oxide cut-off wheels. The combination of a high speed rating and 3M Cubitron™ mineral means you get a cool, sharp, quick cut with minimal product wear.



Product Number	Size (mm)	Order Code	List Price/1	Offer Price/1
01989	75 x 0.8 x 9.5	-0390F	£2.20	£1.76
63104	105 x 1.3 x 9.5	-0454T	£3.14	£2.51

DRONCO Dronco Inox-BF Cutting Discs

High cutting speed, long service life, hardly any burring. For normal steel and stainless steel, suitable for sheet metal and thin-walled profiles.



RPM	Dimensions (mm)	Form	Grade	Order Code DRN-230	List Price/1	Offer Price/1
15250	100 x 1.0 x 16.0	—	AS60	-1010A	£1.39	£1.18
13280	115 x 1.0 x 22.2	—	AS60	-1030C	£1.49	£1.27
13280	115 x 1.6 x 22.2	—	AS46	-1050E	£1.49	£1.27
12200	125 x 1.0 x 22.2	—	AS60	-1070G	£1.59	£1.35
12200	125 x 1.6 x 22.2	—	AS46	-1090J	£1.62	£1.38
8600	180 x 1.6 x 22.2	—	AS46	-1130N	£2.72	£2.31
6600	180 x 2.5 x 22.2	—	AS30	-1140P	£4.08	£3.47
6600	230 x 1.9 x 22.2	—	AS46	-1170S	£3.03	£2.58

NORTON Ultra Thin Wheels

Industrial Line - Type 41 Flat Medium

Advanced grain and bond system for longer life and quicker cutting. Suitable for steel and stainless steel applications. Free from iron, sulphur and chloride.



Size (mm) Dia. x Width x Bore	Grade	Order Code NOR-230	List Price/1	Offer Price/1
100 x 1.6 x 16.0		-3220B	£1.68	£1.26
115 x 1.0 x 22.2	Metal/Inox	-3222D	£1.91	£1.43
115 x 1.6 x 22.2		-3224F	£1.96	£1.47
125 x 1.0 x 22.2		-3226H	£2.05	£1.54
125 x 1.6 x 22.2	Metal/Inox	-3228K	£2.14	£1.61
180 x 1.6 x 22.2		-3230M	£3.14	£2.36
230 x 1.9 x 22.2		-3232P	£5.02	£3.77

Cutting-Off Wheels

Industrial Line - Type 42 DC Medium

Advanced grain and bond system for longer life and quicker cutting. Suitable for steel and stainless steel applications. Free from iron, sulphur and chloride.



Size (mm) Dia. x Width x Bore	Grade	Order Code NOR-230	List Price/1	Offer Price/1
100 x 3.2 x 16.0		-3234R	£1.68	£1.26
115 x 2.5 x 22.2	Metal/Inox	-3236T	£1.88	£1.41
115 x 3.2 x 22.2		-3238W	£1.78	£1.34
125 x 2.5 x 22.2		-3240Y	£1.99	£1.49
125 x 3.2 x 22.2	Metal/Inox	-3242A	£2.00	£1.50
180 x 2.5 x 22.2		-3244C	£3.61	£2.71
180 x 3.2 x 22.2		-3246E	£4.92	£3.69
230 x 2.5 x 22.2	Metal/Inox	-3248G	£5.04	£3.78
230 x 3.2 x 22.2		-3250J	£4.23	£3.17

Grinding Discs

Industrial Line - Type 27 DC Medium

Advanced grain and bond system for longer life and quicker cutting. Suitable for steel and stainless steel applications. Free from iron, sulphur and chloride.



Size (mm) Dia. x Width x Bore	Grade	Order Code NOR-230	List Price/1	Offer Price/1
100 x 7.0 x 16.0		-3252L	£3.19	£2.39
115 x 7.0 x 22.2	Metal/Inox	-3254N	£3.10	£2.33
125 x 7.0 x 22.2		-3256Q	£3.34	£2.51
180 x 7.0 x 22.2	Metal/Inox	-3258S	£5.27	£3.95
230 x 7.0 x 22.2		-3260V	£7.26	£5.45

Chop Saw Wheels - 80m/s

Industrial Line - Type 41 Flat Medium

High performance chop saw wheels with an advanced grain and bond system for longer life and quicker cutting. Internally reinforced for straighter burn and burr free cutting. Designed for small electrical table and fixed machines. For use in the fabrication, foundry and construction industries.



Size (mm) Dia. x Width x Bore	Grade	Order Code NOR-230	List Price/1	Offer Price/1
300 x 2.8 x 25.4		-3650G	£6.19	£4.64
350 x 3.0 x 25.4	Metal	-3652J	£7.39	£5.54
400 x 3.0 x 25.4		-3654L	£14.11	£10.58