

Thrust ball bearings, single direction



Principal dimensions			Basic load ratings		Fatigue load limit	Minimum load factor	Speed ratings		Mass	Designation
d	D	H	dynamic	static	P_u	A	Reference speed	Limiting speed		
mm			kN	C ₀	kN	-	r/min		kg	-
30	47	11	19	43	1,6	0,0096	6000	8500	0,069	51106

