



Sample photo

Order symbol: CAB P 504023
Product nbr: 8104305
Description: Polyester cabinet
Remarks: Grey door

EAN: 6418074050021
El. number:
 Finland 3424137
 Denmark 8212018028
 Sweden 2539821

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key, screws for mounting plate/DIN-rail and wall fastening lugs with screws. Wall mounting screws not supplied.

Dimensions:		L	W	H	Rating:	
mm:	500	400	230	Ingress Protection (EN 60529): IP 66		
inch:	19.7	15.7	9.1	Impact Resistance (EN 50102): IK 10		
Materials:					Electrical insulation: Totally insulated	
Material:	GRP				UV resistance: UL 508	
Base colour:	RAL 7032				Flammability Rating (UL 746 C 5): UL 94 5V	
Cover colour:	RAL 7032				Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws material:	Stainless steel				UL Type: UL TYPE 3, 3R, 3S, 4, 4X, 12, 13	
Gasket material:	Polyurethane				Certificates:	
Temperatures:						
Short term:	-50 ... 150 °C					
Continuous:	-40 ... 70 °C					
Short term:	-60 ... 302 °F					
Continuous:	-40 ... 158 °F					
Accessories:						
MP 5040	Mounting plate					

