

# Sealing frame - CES-B24-SFFS-PLBK - 0801658

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Sealing frame with screw locking, size B24, with flat gasket, for 10 small sleeves



## Key commercial data

Packing unit	1 pc
GTIN	4 046356 674140
Weight per Piece (excluding packing)	173.3 g
Custom tariff number	85472000
Country of origin	Poland

## Technical data

### Dimensions

Length	147 mm
Width	58.5 mm
Height	20 mm

### Ambient conditions

Degree of protection	IP54
	IP65 (when using a CES-SRC../CES-LRC.. cone sleeve and a cable binder)
Ambient temperature (operation)	-40 °C ... 120 °C

### General

Frame type	Sealing frame
Material	PA
Inflammability class according to UL 94	V0
Color	black
Torque	2 Nm ... 4 Nm (Locking screw)
Installation instructions	M4 locking screw with 3 mm Allen screw head, 2 ... 4 Nm torque, 1 large sleeve requires the space of 4 small sleeves, M4 mounting screw

# Sealing frame - CES-B24-SFFS-PLBK - 0801658

## Technical data

### General

	Leak-tightness is guaranteed with underwall and perpendicular mounting; the CES-B24-WRG-BK flat gasket (supplied as standard) should be inserted between the wall and the sealing frame in the case of wall mounting.
--	---

## Classifications

### eCl@ss

eCl@ss 4.0	23110102
eCl@ss 4.1	23110102
eCl@ss 5.0	23110102
eCl@ss 5.1	23110102
eCl@ss 6.0	23110102
eCl@ss 7.0	23110102
eCl@ss 8.0	23110102

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC002498

### UNSPSC

UNSPSC 6.01	27113201
UNSPSC 7.0901	27113201
UNSPSC 11	27113201
UNSPSC 12.01	27113201
UNSPSC 13.2	27113201

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / cULus Recognized

---

#### Ex Approvals

---


#### Approvals submitted


---


### Approval details

## Sealing frame - CES-B24-SFFS-PLBK - 0801658

### Approvals

UL Recognized 

cUL Recognized 

cULus Recognized 

### Accessories

#### Accessories

#### Mounting material

Screw - CES-SFFS-H - 0801728



M4 replacement screw with 4 mm Allen screw head for sealing frame with screw locking

#### Screwdriver tools

Screwdriver - SF-M BH - 1212070



Bit screwdriver, with 1/4" quick-action chuck, handle length 119 mm, 2-component handle, with non-slip grip, suitable for bits according to DIN 3126-C 6.3 and E 6.3/ISO 1173, magnetic

Screwdriver - SF-BIT-HEX 3-50 - 1212647



Screw bit, hexagon, E6.3-1/4" drive, size: Hex 3 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

#### Seal

# Sealing frame - CES-B24-SFFS-PLBK - 0801658

## Accessories


Flat gasket - CES-B24-WRG-BK - 0801727



Flat gasket made of NBR, size B24


## Drawings

Dimensioned drawing



Dimensional drawing

Dimensioned drawing



Panel cutout