




LOC	DIST	REVISIONS					
J	—	変更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			G6	REVISED PER ECO-11-005140	28MAR11	RK	HMR




1. 板厚, 1.6 ± 0.15
(P.C.B. THICKNESS, 1.6 ± 0.15)
2. 公差, ± 0.1
(TOLERANCE, ± 0.1)



- ① 相手ハウジングと所定の機能を満たして嵌合できること。
- ② フードの反りは0.2以内。
3. 推奨取付けねじ：JIS B 1115 又は、1122タッピンねじ
なべ1種、呼び径3を使用し締付け後半田付けする。
4. 適用製品規格 No.108-5093
- ⑤ -A- 面より2mmの範囲で測定のこと。
6. 相手ハウジングとの嵌合力は29.4N以下
但しリセプタクルコンタクトは含まない。
- ④ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION.
- ② WARPAGE 0.2 MAX.
3. RECOMMENDED MOUNTING SCREW; 3mm DIA,
PAN HEAD, CLASS 1 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122.
4. SPEC No.108-5093
- ⑤ TO BE MEASURED WITHIN 2mm FROM -A-
6. IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N MAX. WITHOUT REC CONTACTS.

	SEE CUSTOMER DRAWING 7-171363-1			7-171363-1
	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	2-5171363-1
	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-5171363-1
OBSOLETE	TIN-LEAD		YELLOW	6-171363-7
OBSOLETE	TIN-LEAD		GREEN	6-171363-4
OBSOLETE	TIN-LEAD		NATURAL	6-171363-1
	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	GREEN	2-171363-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	2-171363-1
	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	GREEN	1-171363-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-171363-1
	PRE-TIN		RED	171363-8
	PRE-TIN		YELLOW	171363-7
OBSOLETE	PRE-TIN		GRAY	171363-6
	PRE-TIN		BLUE	171363-5
	PRE-TIN		GREEN	171363-4
	PRE-TIN		BROWN	171363-3
	PRE-TIN		BLACK	171363-2
	PRE-TIN	PRE-TIN BRASS	NATURAL	171363-1
	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
	CONTACT FINISH コンタクト仕上			

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN T.SHINOHARA 31AUG07		 TE Connectivity																				
DIMENSIONS: 単位: 耗 mm			CHK K.BETSUI 31AUG07																						
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 <table><tr><td>0 PLC</td><td>+</td><td>-</td></tr><tr><td>1 PLC</td><td>+</td><td>-</td></tr><tr><td>2 PLC</td><td>+</td><td>-</td></tr><tr><td>3 PLC</td><td>+</td><td>-</td></tr><tr><td>4 PLC</td><td>+</td><td>-</td></tr><tr><td>ANGLES</td><td>+</td><td>-</td></tr></table>		0 PLC	+	-	1 PLC	+	-	2 PLC	+	-	3 PLC	+	-	4 PLC	+	-	ANGLES	+	-	APVD K.BETSUI 31AUG07		NAME 名称 — 17Pos. VERTICAL TYPE CAP HOUSING ASSEMBLY MULTI-INTERLOCK CONNECTOR (WIRE TO P.C.B.)	
				0 PLC	+	-																			
				1 PLC	+	-																			
				2 PLC	+	-																			
3 PLC	+	-																							
4 PLC	+	-																							
ANGLES	+	-																							
PRODUCT SPEC 製品規格 SEE NOTE 4																									
APPLICATION SPEC 取付適用規格 —																									
WEIGHT —																									
(GENERAL TOLERANCE) <table><tr><td>10 0.15</td><td>± 0.2</td></tr><tr><td>10 0.20</td><td>± 0.25</td></tr><tr><td>30 0.30</td><td>± 0.3</td></tr><tr><td>角 度:</td><td>± 3°</td></tr></table>			10 0.15	± 0.2	10 0.20	± 0.25	30 0.30	± 0.3	角 度:	± 3°	MATERIAL 材料 HOUSING: 66NYLON TAB CONTACT: BRASS		FINISH 仕上 表参照 SEE TABLE		CUSTOMER DRAWING		SIZE A2		CAGE CODE 00779		DRAWING NO 番号 C-171363		RESTRICTED TO —		
10 0.15	± 0.2																								
10 0.20	± 0.25																								
30 0.30	± 0.3																								
角 度:	± 3°																								
										SCALE 原 尺 2:1		SHEET 1 of 1		REV G6											