

Datasheet

RS Pro Straight 50Ω Cable Mount TNC Connector, jack, Clamp Termination, URM 43, URM 46

RS Stock No: **546-5250**



Product Details

RS Pro cable mount TNC connector jack is designed for 50 Ω impedance applications. This straight connector jack offers clamp termination. It is suitable for use with URM 43 and URM 46 cables.

Features and Benefits

- Nominal impedance 50Ω
- Suitable for use with URM 43 and URM 46 cables
- Clamp termination

**Specifications:**

Body Orientation	Straight
Cable Type	URM 43, URM 46
Contact Plating	Beryllium Copper
Gender	Female
Impedance	50 Ω
Mounting Type	Cable Mount
Polarity	Normal
Termination Method	Clamp
Dimensions	27 x 14.5 mm
Operating Temperature Range	-65 to +165°C