

## RNGBLANK

Article Number: 851-40196

RapidNet RNG Series Blank, 1/pkg



### Base Data

Local Order Number RNGBLANK

Type RNA-BLANK

Color Black (BK)

- Features and Benefits**
- Plastic blank for partially loaded RNG Series modular panels.
  - 12 port and 6 port RapidNet blanks available.
  - Helps prevent dust and dirt entering the cabinet
  - Easy insertion - clips into panel.

**Product Description** RapidNet is HellermannTyton's patented pre-terminated "connect and go" system which offers a high performance in copper and fiber solutions for data centers and storage area network applications. These pre-terminated solutions do not require on-site termination or certification testing which dramatically reduces installation time up to 85%.

**Port count** 6

**Technical Description** The RapidNet Blanks have a push down clip that fits into the different RapidNet Panels available:  
12 Port Blank (RNAD-BLANK) - RNADUXx-PA1URS-XX.XX, RNADUXx-PA1UCN-XX.XX  
6 Port Blank (RN-BLANK) - RNA6UXx-PA1URS-XX.XX, RNA6UXx-PA1UCN-XX.XX, RNA6G6A-PA1UXx-XX.XX, RNA6G6A-PA1UCN-XX.XX  
4 Port Blank (RN04-BLANK) - RN04-2408-UL  
RapidNet Blanks can also be used with RapidNet Rear Management Panels, RapidNet Hybrid Panels and the Out of Rack solution.

**Short Description** RapidNet RNG Series Blank, 1/pkg

### Product Dimensions

Width W (imperial) 4.0 "

Width W (metric) 102.0 mm

Height H (imperial) 1.1 "

Height H (metric) 27.0 mm

Depth D (imperial) 2.6 "

Depth D (metric) 66.0 mm

### Logistics and Packaging

Package Quantity (imperial) 1

Package Quantity 1

Carton Quantity 1

### Material and Specifications