

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		A1	REVISED PER ECO-11-005033	23MAR11	RK	HMR

1. ALL PARTS PACKAGED UNASSEMBLED.


2 AS SHOWN, THIS KIT CONSISTS OF 2 STRAIN RELIEF HALVES, 2 #4-40 SCREWS, 2 #4-40 NUTS & 2 #4-40 MOUNTING SCREWS.

3 SAME AS SHOWN, EXCEPT: EACH PART IS INDIVIDUALLY BULK PACKED FOR MULTIPLE KIT ORDERS.

4 ZINC PLATED .000200-.000400 THICK, CLEAR CHROMATE COATING.



5 OBSOLETE.

OPENING FOR CABLE
(SEE DASH NO FOR DIA)



SIZE IDENTIFICATION
LETTER MOLDED HERE
(SEE TABLE)

#4-40 FILLISTER HEAD
STEEL SCREW & HEX NUT,
2 EACH REQD. 4



CABLE CLAMP
MATERIAL: FLAME RETARDANT THERMOPLASTIC
FINISH: BRIGHT NICKEL OVER BRIGHT COPPER

#4-40 FILLISTER HEAD SCREW
STEEL, 2 REQD. 4

A	.200	—	5745854-5
C	.250	—	5745854-3
H	.370	5745854-2 5	5745854-1
SIZE IDENT LETTER	CABLE DIA	BULK PACKED KIT NO 3	INDIVIDUAL KIT NO 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER	04AUG05	 TE Connectivity			
		CHK C. ROHDE	04AUG05				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE CLAMP KIT, SIZE 1, 9 POSN, 180 DEGREES, PLATED PLASTIC, AMPLIMITE			
		APVD M. WALMSLEY					
		—		APPLICATION SPEC			
		—		—			
		—		—			
		—		—			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE CALLOUT		SEE CALLOUT		A2		C=5745854	—
CUSTOMER DRAWING				SCALE		SHEET	REV
				2:1		1 of 1	A1