

HERO4 SESSION

SO SMALL. SO STOKED.

KEY CAMERA SPECS

1440p30 / 1080p60 / 720p100 fps

8MP / 10 fps Burst

Control / View / Share

Waterproof to 33' (10m)

GoPro
Be a HERO.



HERO4 Session packs the power of GoPro into our smallest, lightest, most convenient camera yet. Its rugged, waterproof design eliminates the need for a separate housing, while a single button powers on the camera and starts recording automatically. With 1080p60 video and 8MP photos, HERO4 Session delivers the professional image quality that has made GoPro famous.

Product Type	Camera
Product Name	HERO4 Session
Code	GP1038
Retail Barcode	818279014297

FEATURES + BENEFITS

Smallest, Lightest GoPro Yet

With a compact design and weight of just 2.6oz (74g), HERO4 Session is 35% smaller and 40% lighter than other HERO4 cameras.¹

Durable + Waterproof to 33' (10m)

Designed to withstand extreme environments and conditions. Waterproof to 33' (10m), no housing needed.

Easy One-Button Control

A single press of the shutter button powers on the camera and begins capturing video or photos automatically.

Professional Video Quality

Records stunning 1440p30, 1080p60 and 720p100 video.

Powerful Photo Capture

Captures 8MP single photos, 10 fps Burst photos and 0.5-60 second Time Lapse photos.

Easy Access to All Modes + Settings

Access and change all modes and settings using the GoPro App or Smart Remote.²

Built-In Wi-Fi + Bluetooth®

Enables connectivity to the GoPro App or Smart Remote² to control the camera remotely, and view and share your content.

Compatible With GoPro Mounts + Accessories

Works with GoPro mounts and GoPro accessories for immersive self-capture of your favorite activities.

Ultimate Mounting Flexibility

The camera can be rotated in mounting frames to create ultra compact mounting setups, while the Ball Joint Buckle lets you adjust capture angles instantly.

Dual Mic System

Dynamically switches microphones for reduced wind noise and enhanced audio in high-speed or windy environments.

Auto Image Rotation

Automatically adjusts capture orientation to right-side up when the camera is mounted upside down.

Protune™ for Video

Delivers minimally compressed, cinema-caliber video optimized for professional productions.

SuperView™

Captures the world's most immersive wide-angle field of view.

Auto Low Light

Automatically adjusts frame rates for optimal low-light performance.

Expandable External Memory

Supports Class 10 or UHS-I microSD cards up to 64GB.²

Built-In Battery

Rechargeable built-in battery offers up to two hours of recording time.³

GoPro App + GoPro Studio

Control your camera remotely. View and share your content. Easily create gorgeous, GoPro-style videos.


DEFAULT CAMERA MODES

VIDEO		
RESOLUTION	FPS (NTSC/PAL)	FIELD OF VIEW (FOV)
1080p (16:9)	30	Ultra Wide

ADDITIONAL MODES AVAILABLE USING GOPRO APP OR SMART REMOTE

VIDEO		
RESOLUTION	FPS (NTSC/PAL)	FIELD OF VIEW (FOV)
1440p (4:3)	30, 25	Ultra Wide
1080p (16:9)	60, 50, 30, 25	Ultra Wide, Medium
1080p SuperView™ (16:9)	48, 30, 25	Ultra Wide
960p (4:3)	60, 50, 30, 25	Ultra Wide
720p (16:9)	100, 60, 50, 30, 25	Ultra Wide, Medium
720p SuperView (16:9)	60, 50, 30, 25	Ultra Wide
WVGA (16:9)	120, 100	Ultra Wide

PHOTO



Time Lapse
0.5 second intervals

PHOTO






Photo
8MP (Ultra Wide)



Burst
8MP @ 10 fps



Time Lapse
0.5, 1, 2, 5, 10, 30, 60 second intervals

+ ACCESS
ALL MODES
+ SETTINGS
VIA



GOPRO APP
(Free)

OR



SMART REMOTE
(Sold Separately)

KEY CAMERA SPECS

- Video: 1440p30 / 1080p60 / 960p60 / 720p100 fps
- Photo: 8MP / 10 fps Burst
- Waterproof to 33' (10m)
- Built-In Wi-Fi + Bluetooth®
- Protune™ for Video
- Dual Mic System
- Auto Image Rotation
- SuperView™
- Auto Low Light
- HiLight Tag

IMAGE ASSETS



CAPTURE. CREATE. SHARE.



GOPRO APP + GOPRO STUDIO

Expand your GoPro experience. View and share your content. Easily create gorgeous, GoPro-style videos.