

**General Information**

Extended Product Type:	FEM8S
Product ID:	1SNA103923R1500
EAN:	3472591039238
Catalog Description:	FEM8S End Sections Orange
Long Description:	FEM8S - End Sections - Orange - 1.5mm Spacing

**Categories**

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Sections

**Ordering**

EAN:	3472591039238
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

**Dimensions**

Product Net Weight:	2.6 g
---------------------	-------

**Container Information**

Package Level 1 Units:	20 piece
Package Level 1 Gross Weight:	0.052 kg
Package Level 1 EAN:	3472591039238
Package Level 2 Units:	1000 piece

**Environmental**

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
--------------------------	------------------------------------------------------

**Technical UL/CSA**

Flammability According to UL94:	V0
---------------------------------	----

**Additional Information**

Ambient Temperature:	-5 ... +40 °C
Color:	Orange
Function:	End Sections
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Product Main Type:	FEM8
Product Name:	End Section
Spacing:	1.5 mm
Suitable For:	M4/8.SF M4/8.SN

**Certificates and Declarations (Document Number)**

Declaration of Conformity - CE:	1SND225002C1007
RoHS Information:	1SND230478F0202

**Classifications**

ETIM 4.0:	EC000886 - Endplate and partition plate for terminal block
ETIM 5.0:	EC000886 - Endplate and partition plate for terminal block
Object Classification Code:	X

