



Sample photo

Order symbol: AL 121208
Product nbr: 7011210

Description: Enclosure
Remarks: Aluminium

EAN:	6418074004154
El. number:	
Finland	3423617
Denmark	8212004689
Italy	7321050
Sweden	2536319

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	L	W	H
mm:	125	124	81
inch:	4.9	4.9	3.2

Materials:

Material:	AL
Base colour:	RAL 7001
Cover colour:	RAL 7001
Cover screws material:	Stainless steel
Gasket material:	Polyurethane

Temperatures:

Short term:	-50 ... 140 °C
Continuous:	-50 ... 80 °C
Short term:	-60 ... 285 °F
Continuous:	-60 ... 175 °F

Accessories:

AM 1212	Mounting plate
ARH 12	DIN-35 Mounting rail
MR 75005	Taptite screw
MRS 28541	Wall fastening lug set
PH A & AH A/B	Hinge set

Rating:

Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 08
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:

Underwriters Laboratories
UL Canada

