

## Datasheet

# RS Pro Round Fixed Height Feet, PD.2150BL 16mm, PUR, +65°C -34°C

RS Stock No: **223-578**



## Product Details

RS Pro round anti-vibration feet in black colour, is made with PUR for long life durability. It has a diameter of 16 mm and overall height of 7.9 mm. It features excellent skid resistance with a high coefficient of friction and excellent resistance to moving and staining. It has a temperature rating of -34 to +65°C. This flexible polyurethane feet is suitable for indoor and limited outdoor applications.

## Features and Benefits

- Long ageing resiliency and will not crack or harden
- Ideal for use on glass, aluminium, stainless steel, acrylic plastic, polyethylene, polystyrene, ABS, polypropylene and polycarbonate
- To ensure maximum adhesion, surfaces must be clean, dry and well unified
- Flexible polyurethane feet suitable for indoor and limited outdoor applications



ENGLISH

### Specifications:

|                               |                  |
|-------------------------------|------------------|
| Foot Colour                   | Black            |
| Foot Shape                    | Round            |
| Material                      | PUR              |
| Mounting Type                 | Adhesive         |
| Type                          | Feet             |
| Diameter                      | 16 mm            |
| Maximum Operating Temperature | +65°C            |
| Minimum Operating Temperature | -34°C            |
| Overall Height                | 7.9 mm           |
| Finish                        | Gloss            |
| Hardness                      | 65 to 70 Shore A |