



FEMALE END VIEW



SPECIFICATIONS

| | |
|--------------------------------|----------------------------------|
| CONTACT CARRIER MATERIAL/COLOR | NYLON OR TPU/BLACK |
| MOLDED HEAD MATERIAL/COLOR | TPU/RED |
| CONTACT MATERIAL/PLATING | BRASS/GOLD |
| COUPLING NUT MATERIAL/PLATING | BRASS/NICKEL |
| RATED CURRENT [A] | 4.0 A |
| RATED VOLTAGE [V] | 125 VAC/VDC |
| TEMPERATURE RANGE | -40°C to +80°C (-40°F to +176°F) |
| PROTECTION CLASS | MEETS NEMA 1,3,4,6P AND IEC IP67 |



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "/S1055" DESIGNATES RED MOLD BODY.

| | | | | | | | |
|----------------------|--|---|--|--|--|--|--|
| RELATED DOCUMENTS | | 3RD ANGLE PROJECTION | | THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. | | TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com | |
| 1. 2. 3. 4. | | | | DRFT CK | | DATE 09/01/11 | |
| MATERIAL | | ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY | | DSGN | | SCALE 1=.5 | |
| SEE SPECIFICATIONS | | CONTACT TURCK FOR MORE INFORMATION | | UNIT OF MEASUREMENT | | DESCRIPTION | |
| FINISH | | MILLIMETER [INCH] | | DO NOT SCALE THIS DRAWING | | IDENTIFICATION NO. U0946-04 REV A | |
| SEE SPECIFICATIONS | | | | | | PKG 3M-J13/S1055 FILE: U0946-04 SHEET 1 OF 1 | |

| | | | | |
|-----|-----------------|----|----------|---------|
| A | DRAWING RELEASE | CK | 09/02/11 | |
| REV | DESCRIPTION | BY | DATE | ECO NO. |