

EK EKWH 250 G NEW



Sample photo

Order symbol: EKWH 250 G NEW
Product nbr: 2538990
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074048547
EI. number:
Finland: 3420013
Electric No. Sweden: 2538090

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:		
Length	Width	Height			
mm:	760	560	250	EKW 100-G NEW	Cover
inch:	29.9	22.0	9.8	EKWH	Base, PC
Materials:			Rating:		
Material:	Polycarbonate		EKW 100-G	Cover	
Base colour:	RAL 7035 -light grey		EKUVT	Mounting plate	
Cover screws material:	Polyamide		EKUXT	Mounting plate isolated	
Cover colour:	RAL 7035 -light grey				
Cover screws colour:	Grey				
Gasket material:	Polyurethane				
Temperatures:			Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (short term):	-40 ... 120 °C		Impact Resistance (EN 62262): IK08/IK09		
Temperature °C (continuous):	-40 ... 80 °C		Electrical insulation: Totally insulated		
Temperature °F (short term):	-40 ... 250 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (continuous):	-40 ... 175 °F		UV resistance: UL 508		
Accessories:			Flammability Rating: UL 746C 5"		
EKWH NEW	Base, PC		Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12		
			Certificates:		
			SGS Fimko		
			Gost R		

