




RECOMMENDED PC BOARD MOUNTING DIMENSIONS
RECOMMENDED STENCIL THICKNESS = 0.25 [.010]

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
U1		REVISED PER ECO-10-000443		13JAN10	KK	HMR	

PART NO.	SUPERSEDED BY
1-104362-2	1-104909-2
1-104362-4	1-104909-4
1-104362-7	1-104909-7
2-104362-2	—
2-104362-3	—

10	33.02	[1.300]	30.99	[1.220]	27.94	[1.100]	11	12	6-104362-1
10	30.48	[1.200]	28.45	[1.120]	25.4	[1.000]	10	11	6-104362-0
10	27.94	[1.100]	25.91	[1.020]	22.86	[.900]	9	10	5-104362-9
10	25.4	[1.000]	23.37	[.920]	20.32	[.800]	8	9	5-104362-8
10	22.86	[.900]	20.83	[.820]	17.78	[.700]	7	8	5-104362-7
10	20.32	[.800]	18.29	[.720]	15.24	[.600]	6	7	5-104362-6
10	17.78	[.700]	15.75	[.620]	12.7	[.500]	5	6	5-104362-5
10	15.24	[.600]	13.21	[.520]	10.16	[.400]	4	5	5-104362-4
10	12.7	[.500]	10.67	[.420]	7.62	[.300]	3	4	5-104362-3
10	10.16	[.400]	8.13	[.320]	5.08	[.200]	2	3	5-104362-2
10	7.62	[.300]	5.59	[.220]	2.54	[.100]	1	2	5-104362-1
	66.04	[2.600]	64.01	[2.520]	60.96	[2.400]	24	25	2-104362-4
	63.5	[2.500]	61.47	[2.420]	58.42	[2.300]	23	24	2-104362-3
	60.96	[2.400]	58.93	[2.320]	55.88	[2.200]	22	23	2-104362-2
	58.42	[2.300]	56.39	[2.220]	53.34	[2.100]	21	22	2-104362-1
	55.88	[2.200]	53.85	[2.120]	50.8	[2.000]	20	21	2-104362-0
	53.34	[2.100]	51.31	[2.020]	48.26	[1.900]	19	20	1-104362-9
	50.8	[2.000]	48.77	[1.920]	45.72	[1.800]	18	19	1-104362-8
	48.26	[1.900]	46.23	[1.820]	43.18	[1.700]	17	18	1-104362-7
	45.72	[1.800]	43.69	[1.720]	40.64	[1.600]	16	17	1-104362-6
	43.18	[1.700]	41.15	[1.620]	38.1	[1.500]	15	16	1-104362-5
	40.64	[1.600]	38.61	[1.520]	35.56	[1.400]	14	15	1-104362-4
	38.1	[1.500]	36.07	[1.420]	33.02	[1.300]	13	14	1-104362-3
	35.56	[1.400]	33.53	[1.320]	30.48	[1.200]	12	13	1-104362-2
1	33.02	[1.300]	30.99	[1.220]	27.94	[1.100]	11	12	1-104362-1
1	30.48	[1.200]	28.45	[1.120]	25.4	[1.000]	10	11	1-104362-0
1	27.94	[1.100]	25.91	[1.020]	22.86	[.900]	9	10	104362-9
1	25.4	[1.000]	23.37	[.920]	20.32	[.800]	8	9	104362-8
1	22.86	[.900]	20.83	[.820]	17.78	[.700]	7	8	104362-7
1	20.32	[.800]	18.29	[.720]	15.24	[.600]	6	7	104362-6
1	17.78	[.700]	15.75	[.620]	12.7	[.500]	5	6	104362-5
1	15.24	[.600]	13.21	[.520]	10.16	[.400]	4	5	104362-4
1	12.7	[.500]	10.67	[.420]	7.62	[.300]	3	4	104362-3
1	10.16	[.400]	8.13	[.320]	5.08	[.200]	2	3	104362-2
1	7.62	[.300]	5.59	[.220]	2.54	[.100]	1	2	104362-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

MATERIAL

DWN G DOUTY 2-22-88
CHK T C CLARK 2-22-88
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -
CUSTOMER DRAWING

2-22-88
NAME
SIZE A2
CAGE CODE 00779
DRAWING NO C=104362
SCALE 4:1
SHEET 1 OF 1
REV U1

Tyco Electronics
Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

HEADER ASSY, AMPMODU MTE, VERTICAL
SINGLE ROW, .100 C/L, .025 SQ POST
POLARIZED, WITH LATCHING & HOLD DOWN

AMP 1471-9 REV 31MAR2000