Datasheet

Art.No. R1.190.1310.0

Configurable control component SP-COP2-ENI-A DC 24V

samosPRO-Compact module, 16 safe inputs, 4 safe outputs, 4 configurable safe I/O, USB-Interface, Industrial-Ethernet, Pluggable screw-terminals

Art.No.	R1.190.1310.0
EAN	4049088257780
Order unit	1 pieces

Approvals

Technical data

Connection Data

Type of electric connection	Screw connection
Detachable clamps	Yes

Output circuit

Number of outputs	8
Output current	4 A
Short-circuit protection, outputs	Yes
Type of digital output	Transistor
Min. allowed output voltage	16.2 V
Max. allowed output voltage	30 V
Number of digital outputs, integrated	8

Control circuit

Min. rated DC voltage for controls	15.6 V
Max. rated DC voltage for controls	30 V
Input current with signal 1	2.3 mA
Permitted voltage at input	30 V

Supply circuit

Min. supply voltage	16.8 V
Max. supply voltage	30 V

Dimensions

Depth	115 mm
Width	45 mm
Height	96 mm

Classification

ETIM 5.0	EC002538: Configurable control component
ETIM 4.0	EC002538: Configurable control component

Drawings


96,4
57,7
120,7
45
45
Teile-Nr. / Part-No.
Typ / Type
R1.190.1110.0
SP-COP1-A
R1.190.1210.0
SP-COP2-EN-A
R1.190.1310.0
SP-COP2-ENI-A
www.wieland-electric.com
eshop.wieland-electric.com
T R1.190.1110.0 /01K
Schraubsteckblockklemme
samosPRO SP-COP1/2