

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR - SWITCH

CATALOG LISTING

JV - 7

(M) JV - 7
ISSUE 3

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

JV - 7

M

DRAWING
NUMBER



ISSUE

6

4 - 40 NC X .625 REF ROUND HEAD MACHINE
SCREW (PART NO. JV-10008) (2)

4 - 40 NC HEX NUT
(PART NO. JV-10007) (2)

LOCKWASHER
(PART NO. JV-10254) (2)



NOTE -
△ - FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH V3-1 BASIC SWITCH INSTALLED

OPERATING FORCE ----- 15 OZ MAX
RELEASE FORCE ----- 6 OZ MIN
PRETRAVEL ----- .062 MAX
DIFFERENTIAL TRAVEL ----- .025 MAX
OVERTRAVEL ----- .050 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT

FO-50378

DRAWN

K L B

JUNE 59

JUNE '59

JUNE '59

CHECK

CHECK

CHECK