

**EURONORD AL 165609**



Sample photo

|                      |           |
|----------------------|-----------|
| <b>Order symbol:</b> | AL 165609 |
| <b>Product nbr:</b>  | 7011330   |
| <b>Description:</b>  | Enclosure |
| <b>Remarks:</b>      | Aluminium |

|                    |               |
|--------------------|---------------|
| <b>EAN:</b>        | 6418074004215 |
| <b>El. number:</b> |               |
| Finland:           | 3423629       |
| Denmark:           | 8212004760    |
| Italy:             | 7321080       |
| Sweden:            | 2536331       |

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

| Dimensions:            |  | Length                     | Width | Height | Rating:                                 |
|------------------------|--|----------------------------|-------|--------|-----------------------------------------|
| mm:                    |  | 560                        | 160   | 90     | Ingress Protection (EN 60529): IP 66/67 |
| inch:                  |  | 22.0                       | 6.3   | 3.5    | Impact Resistance (EN 62262): IK 08     |
| Materials:             |  |                            |       |        | NEMA Class: NEMA 1, 4, 4X, 12, 13       |
| Material:              |  | Aluminium                  |       |        | Certificates:                           |
| Base colour:           |  | RAL 7001                   |       |        | Underwriters Laboratories               |
| Cover colour:          |  | RAL 7001                   |       |        | Fimko                                   |
| Cover screws material: |  | Stainless steel            |       |        | UL Canada                               |
| Gasket material:       |  | Neoprene                   |       |        | Gost R                                  |
| Temperatures:          |  |                            |       |        |                                         |
| Short term:            |  | -50 ... 140 °C             |       |        |                                         |
| Continuous:            |  | -50 ... 80 °C              |       |        |                                         |
| Short term:            |  | -60 ... 285 °F             |       |        |                                         |
| Continuous:            |  | -60 ... 175 °F             |       |        |                                         |
| Accessories:           |  |                            |       |        |                                         |
| AM 1656                |  | Mounting plate             |       |        |                                         |
| ARH 1656               |  | DIN-35 Mounting rail       |       |        |                                         |
| MRS 28541              |  | Wall fastening lug (2 pcs) |       |        |                                         |
| PH A & AH A/B          |  | Hinge set                  |       |        |                                         |

