

# EXFM05

JOINT WASHER 25MM



Sealing Joint Washer, M25 Metric Thread, Outside Diameter 34.3 Millimeters, Thickness 1.7 Millimeters, Nylon

## General Information

Extended Product Type	• EXFM05
Product ID	• 7TCA297150R0040
EAN	• 5011949011311
Catalog Description	• JOINT WASHER 25MM
Long Description	• Sealing Joint Washer, M25 Metric Thread, Outside Diameter 34.3 Millimeters, Thickness 1.7 Millimeters, Nylon

## Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	3926909996

## Dimensions

Product Net Weight	68.04 g
--------------------	---------

## Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	71.12 mm
Package Level 1 Height	152.4 mm
Package Level 1 Length	25.4 mm

Package Level 2 Units	10 piece
Package Level 2 Width	25.4 mm
Package Level 2 Height	25.4 mm
Package Level 2 Length	25.4 mm

---

**Additional Information**

---

Brand Label	Kopex
Color	Yellow
Material	Nylon
Product Main Type	KOPEX-EX FLEXIBLE CABLE PROTECTION
Product Name	Plastic washer
Product Type	Sealing Joint Washer

---

**Classifications**

---

ETIM 6	EC001181 - Sealing ring
UNSPSC	31161818

