

Datasheet

**RS Pro Zinc Plated Steel Adjustable Height Mount 140mm
Rubber 115mm 60mm 169mm 2000kg 120mm M20 3.5°
RS Stock No: 283-2764**



Product Details

RS Pro zinc plated steel adjustable mount is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. The zinc plated steel machine mount is suitable for use in less demanding environments. The built in levelling bolt means the mount can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability.

Features and Benefits

- Long bolt offers height adjustment
- Compensates with up to 7° swivel
- Rubber foot

**Specifications:**

Base Material	Zinc Plated Steel
Diameter	140 mm
Foot Material	Rubber
Maximum Adjustment Height	115 mm
Minimum Adjustment Height	60 mm
Overall Height	169 mm
Static Load Capacity	2000 kg
Thread Length	120 mm
Thread Size	M20
Tilt Angle	3.5°