

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39484-0011](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 4.00mm Pitch Positive Locking Terminal Block Plug, Tin Plating, 11 Circuits

Documents:

[3D Model](#) [Product Specification PS-39484-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	39484
Application	N/A
Component Type	Plug
Overview	Eurostyle™ Terminal Blocks
Product Name	Eurostyle™ Pluggable
Type	Euro Block
UPC	883906383039

Physical

Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Black
Entry Angle	Vertical (Top Entry)
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PCB Retention	None
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +140°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24


Electrical

Current - Maximum per Contact	10A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Product Specification	PS-39484-001
Sales Drawing	SD-39484-001



EU RoHS

RoHS Compliant by Exemption
REACH SVHC Not Reviewed
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[39484Series](#)

Mates With

39485 4.00mm Pitch Tin Plated PCB Headers