



ENGLISH

## Datasheet

### LED Cluster Lamp, White, 90 mA, 230 V ac

Stock Number: 720-3805



- Direct **drop-in replacement**
- **No need to remove the magnetic ballast**
- **50,000 hours** life expectancy
- **Super-bright** - > 64 lumens per watt
- Consume only **7W** and **14W**
- **2-pin** or **4-pin**

Schools

Hospitals

Car Parks

Universities / Colleges

Sports Centres

Stairways and Corridors

Wash Rooms

Hotels

Bars / Pubs

Clubs

Warehouses

Cold Rooms



**Lamp**

Colour Temperature

Pure White (5000°K)

Warm White (3250°K)

Lamp Life

up to 50,000 hours

Built in redundancy against LED failure

**Environmental**

Operating Temperature

-20°C...+30°C

Storage Temperature

-40°C...+65°C

Relative Humidity

0% to 90% Non-condensing

**Materials**

Case

Flame-retardant ABS V0 rated

Lens

Polycarbonate V2 rated

**Voltage & Connection**

230 V ac +/- 5% (see label), 50 Hz

Internal fuse protection

200mA (not user replaceable)

Remove the starter and any power factor capacitor installed in the fitting. **Any modification required to the fitting should be undertaken only by a qualified electrician.** The owner/ installer must satisfy themselves that the lamp is suitable for use and may be used safely in a given fitting.