











RECEPTACLE

PLUG




SHOWN WITH STANDARD EAR



SHOWN WITH STANDARD EAR

UPDATE TITLE BLOCK EC NO: UCP2006-1431 DRAWN: AELHAG 2006/08/29 CHKD: SCHMIDT 2006/08/29 APPR: FSN TH 2006/08/30	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY	DATE	.062/(1.57) HOUSING PLUG & RECEPTACLE 6 CKT, .145/(3.68) C.L. MOLEX INCORPORATED			
				4 PLACES ± .010	± .010	KBW	7/22/88				
				3 PLACES ± .010	± .010	CHECKED BY	DATE				
				2 PLACES ± 0.25	± .014	RW	7/22/88	SD-1625-6*			
				1 PLACE ± 0.35	± .014	APPROVED BY	DATE				
				ANGULAR ± 1/2°		RAS	7/22/88				
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
						SEE CHART		SD-1625-6*		1 OF 2	
						SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



PLUG

ORDER NO	ENG NO	
03-06-2062	I625-6P	
03-06-2061	I625-6P I	
03-06-7062	I625-6PBK	
03-06-7061	I625-6P IBK	
03-06-7063	I625-6POR	OBSOLETE
- -		

LEGEND:

1625-6****

CIRCUIT SIZE

P = PLUG
R = RECEPTACLE


BLANK = WITH STANDARD EARS
1 = WITHOUT EARS
2 = WITH PREBENT EARS

COLOR:

BLANK = NATURAL COLOR
AM = AMBER BK = BLACK BU = BLUE
BN = BROWN GY = GRAY GN = GREEN
OR = ORANGE RD = RED YW = YELLOW



RECEPTACLE

ORDER NO	ENG NO	
03-06-1061	I625-6R	
03-06-1062	I625-6R I	
03-06-6061	I625-6RBK	
03-06-6062	I625-6R IBK	
03-06-6063	I625-6ROR	OBSOLETE
03-06-6064	I625-6RBU	
NOT TOOLED	I625-6R2	




DETAIL A

.062/(1.57) STANDARD MOUNTING EAR
(SCALE 4:1)



HOUSING	DIM. "A"	DIM. "B"	"C" PREBENT EAR	"C" STANDARD EAR
PLUG	.607/(15.42)	.615/(15.62)	.22/(5.6)	.18/(4.6)
RECEPT.	.505/(12.83)	.552/(14.02)	.23/(5.8)	.19/(4.8)



DETAIL B

.062/(1.57)PREBENT MOUNTING EAR
(SCALE 4:1)

- NOTES:-
1. MATERIAL NYLON TYPE 6/6. 94-2.
 2. FINISH: NONE.
 3. PRODUCT SPECS: MOLEX PRODUCT SPECS 02-06 APPLIES.
 4. PACKAGING SPECS: BULK PACK PER PK-1625-001.

REINSTATE PARTS EC NO: UCP2006-1431 DRWNAELHAG 2006/08/29 CHKD:LSHMDT 2006/08/29 APPR:FSM TH 2006/08/30	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
		mm	INCH	DRAWN BY KBW	DATE 7/22/88	TITLE .062 / (1.57) HOUSINGS PLUG & RECEPTACLE 6 CKT, .145/(3.683) C.L.		
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY RW	DATE 7/22/88	moLEX MOLEX INCORPORATED		
		2 PLACES ± 0.25 ± .014	1 PLACE ± 0.35 ± ---	APPROVED BY RAS	DATE 7/22/88			
ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-1625-6*		2 OF 2		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								