





注記：
△ **-A-** 面より2mmの範囲で測定のこと。
△ 相手ハウジングと所定の機能を満たしてかん合できること。
△ フードの反りは0.2以内。
4 推奨取付けねじ：JIS B 1115 又は、1122 タッピンねじ
なべ1種又は2種、呼び径3長さ6mm以下
(締め付けトルク：39.2N 以下)
5 適用製品規格 No.108-5093
6 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。
△ タブなしタイプ(表参照)回路番号下図参照のこと。

NOTES:
△ TO BE MEASURED WITHIN 2mm FROM **-A-**
△ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES
FUNCTION
△ WARPAGE 0.2 MAX.
4 RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH<MAX.>
PAN HEAD, CLASS 1 AND 2 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122 <TIGHTENING TORQUE; 39.2N MAX.>
5 SPEC. No. 108-5093
6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N MAX WITHOUT RECEPTACLE CONTACT
△ NON TAB CONTACT'S TYPE <SEE TABLE>
CIRCUIT NUMBER



	--	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μ m MIN.)	NATURAL	5172040-8
	--	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	1-5172040-5
	2	PRE-TIN		NATURAL	2-172040-1
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	GREEN	1-172040-8
	--	TIN-LEAD	SELECTIVE GOLD (0.38μ m MIN.)	NATURAL	1-172040-5
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	YELLOW	1-172040-4
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	GRAY	1-172040-3
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	BLUE	1-172040-2
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	GREEN	1-172040-1
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	BROWN	1-172040-0
OBSOLETE	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	BLACK	172040-9
	--	TIN-LEAD	SELECTIVE GOLD (0.76μ m MIN.)	NATURAL	172040-8
OBSOLETE	--	PRE-TIN		YELLOW	172040-7
OBSOLETE	--	PRE-TIN		BLUE	172040-5
	--	PRE-TIN		GREEN	172040-4
OBSOLETE	--	PRE-TIN		BROWN	172040-3
	--	PRE-TIN		BLACK	172040-2
	--	PRE-TIN		NATURAL	172040-1
	△NON TAB PLACES タブなし箇所	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上					

TOLERANCE UNLESS
OTHERWISE SPECIFIED:
一般公差
0<X≤ 10 : ±0.2
10<X≤ 30 : ±0.25
30<X≤ 100 : ±0.3
ANGLE : ±3°
角度

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 31AUG07	Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: 特 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	CHK K.BETSUI 31AUG07	NAME 名称	
		APVD K.BETSUI 31AUG07	PRODUCT SPEC 製品規格 108-5093	
		APPLICATION SPEC 取付適用規格	SIZE A2	
MATERIAL 材料 HSG: 66 NYLON CONTACT: BRASS	FINISH 仕上	WEIGHT -	CAGE CODE 00779	DRAWING NO 番号 172040
CUSTOMER DRAWING			SCALE 尺度 2:1	SHEET 1 of 1
			REV G4	RESTRICTED TO