

6

5

4

3

2



1

NOTES:

1 PRODUCT LABELED & PACKAGED COMPLETE

2 CATALOG NUMBER, AMP & VOLTAGE RATING, DATE CODE, AND WOODHEAD LOGO, TO BE PRINTED ON CABLE.

FACE VIEW



PART No.	CABLE LENGTH
L04300M78M050	5 METER
L04300M78M100	10 METER

REMOVE LOGO/UPDATE MOLD EC NO: WNA2010-0108 DRWN: LHARTMAN 8/17/09 CHKD: TWOLDEGE2009/09/22 APPR: JFMURPHY 2009/10/26	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY QW	DATE 1998/10/19	TITLE M16 HOME RUN CABLE 14 POLE FEMALE STRAIGHT		
		4 PLACES	±---	±---	CHECKED BY BP	DATE 1998/10/19			
		3 PLACES	±---	±---	APPROVED BY JFMURPHY		DATE 2009/10/23	MOLEX INCORPORATED	
2 PLACES	±---	±---	MATERIAL NO.		SEE TABLE	DOCUMENT NO. L04300M	SHEET NO. 1 OF 1		
1 PLACE	±---	±---	ANGULAR ±1/2°		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A						

6

5

4

3

2

1