



4

3

2

1

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J	—		D1	REVISED PER ECO-11-005140	28MAR11



1. 嵌合相手ハウジング型番 ; 917319

2. 内装するリセコンタクト型番 ; 917308


3. 適用製品規格番号 ; 108-5426

4. 取扱説明書 ; 412-5653-1
1. THE MATING PLUG HSG P/N 917319

2. APPLIED CONTACT P/N 917308

3. APPLICABLE PRODUCT SPEC No.108-5426

4. INSTRUCTION SHEET:412-5653



SECT. A-A

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
0 < x ≤ 10	: ±0.2
10 < x ≤ 30	: ±0.25
30 < x ≤ 100	: ±0.3
ANGLE ; 角度	: ±0.3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. YAMAGUCHI 31JUL02	TE Connectivity			
DIMENSIONS: 単位: 耗 mm		CHK T. HAYASHI 02AUG02				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD H. YAMAGAMI 02AUG02	NAME 名称 MINI MULTI LOCK CONNECTOR 7POS PLUG HSG			
MATERIAL 材料 PBT G		PRODUCT SPEC 製品規格 SEE TABLE	SIZE A3		CAGE CODE 00779	DRAWING NO 番号 C-917318
FINISH 仕上 SEE TABLE		APPLICATION SPEC 取付適用規格	WEIGHT 0.85g		RESTRICTED TO —	
CUSTOMER DRAWING			SCALE 尺度 5:1		SHEET 1 OF 1	REV D1