



360C - 4-Piece Quick Change Convertible Retaining Ring Pliers Set



Features and Benefits

- This Quick Change Design Convertible Retaining Ring Pliers Set has 4 pieces
- Overall length for the pliers ranges from 5-3/4" to 7-1/4"
- Two pieces meet ergonomic criteria
- Weighs 1.26 pounds
- Patented plier design permits quick change-over to work internal or external rings
- Pliers have no screws to tighten
- Pliers have a return spring to reduce fatigue and facilitate operation
- Pliers have air cushioned grips which spreads loads across the hand increasing comfort

Product Details

Weight 1.26 lbs

Product Contents (Displaying 4 of 4) [View Complete List](#)

Item #	Description
399L	.038 18° Tip Quick Change Convertible Retaining Ring Pliers
371L	.038 90° Convertible Retaining Ring Pliers
385L	.070 18° Tip Convertible Retaining Ring Pliers
376L	.070 90° Tip Convertible Retaining Ring Pliers



399L - .038 18° Tip Quick Change Convertible Retaining Ring Pliers



Features and Benefits

- These Convertible Retaining Ring Pliers have a Quick Change Design and a 18° tip angle
- .038 Tip size
- 6" Overall length
- Meets Ergonomic criteria
- Patented design permits quick change-over to work internal or external rings
- No screws to tighten or come loose
- Spring return to reduce fatigue and facilitate operation
- Air-Pocket cushion grip spreads loads across the hand increasing comfort
- Fixed tips are precision formed and induction hardened for accurate fit and long wear

Product Details

Length	6"
Tip Angle (degrees)	18
Tip Size	.038
Anderton External Ret. Ring	1400 1401
Dash No. External (Internal)	-25 thru -66 (-37 thru -56)
Industrial External Ret. Ring	3100 3101
External Shaft Diameter	1/4 - 43/64
Truarc External Ret. Ring	5100 5101
Anderton Internal Ret. Ring	N1300 N1301
Internal Bore Diameter	3/8 - 9/16
Industrial Internal Ret. Ring	3000-X 3001-X
Truarc Internal Ret. Ring	N5000 N5001



- Use safety goggles. Serious eye injury is possible.
- Do not use pliers with cushion grips on active electronics – there is no insulation.
- Do not use extenders or cheater bars on plier handles.
- Shield yourself and bystanders when using retaining ring pliers. Flying objects possible.
- Cut wire back in jaws – not at tip.
- Prevent exposure to excessive heat.



371L - .038 90° Convertible Retaining Ring Pliers



Features and Benefits

- These Convertible Retaining Ring Pliers have a Quick Change Design and a 90° tip angle
- .038 Tip size
- 5-3/4" Overall length
- Patented design permits quick change-over to work internal or external rings
- No screws to tighten or come loose
- Spring return to reduce fatigue and facilitate operation
- Air-Pocket cushion grip spreads loads across the hand increasing comfort
- Fixed tips are precision formed and induction hardened for accurate fit and long wear

Product Details

Length	5-3/4"
Tip Angle (degrees)	90
Tip Size	.038

Anderton External Ret. Ring	1408 1440
-----------------------------	--------------

Dash No. External (Internal)	-50 thru -78 (-37 thru -56) -12 thru -25 (-75 thru -100)
------------------------------	---

Industrial External Ret. Ring	4100
-------------------------------	------

External Shaft Diameter	1/2 - 25/32 1/8 - 5/32
-------------------------	---------------------------

Truarc External Ret. Ring	5108 5555
---------------------------	--------------

Anderton Internal Ret. Ring	N1302 1308
-----------------------------	---------------

Internal Bore Diameter	3/8 - 9/16 3/4 - 1
------------------------	-----------------------

Industrial Internal Ret. Ring	4000
-------------------------------	------

Truarc Internal Ret. Ring	N5002 5008
---------------------------	---------------



- Use safety goggles. Serious eye injury is possible.
- Do not use pliers with cushion grips on active electronics – there is no insulation.
- Do not use extenders or cheater bars on plier handles.
- Shield yourself and bystanders when using retaining ring pliers. Flying objects possible.
- Cut wire back in jaws – not at tip.
- Prevent exposure to excessive heat.



385L - .070 18° Tip Convertible Retaining Ring Pliers



Features and Benefits

- These Convertible Retaining Ring Pliers have a Quick Change Design and an 18° tip angle
- .070 Tip size
- 7-1/4" Overall length
- Patented design permits quick change-over to work internal or external rings
- No screws to tighten or come loose

Product Details

Length	7-1/4"
Tip Angle (degrees)	18
Tip Size	.070
Anderton External Ret. Ring	1400 1401 1402
Dash No. External (Internal)	-93 thru -143 (-106 thru -175) -100 thru -143 (-106 thru -175)
Industrial External Ret. Ring	3100 3101
External Shaft Diameter	15/16 - 1-7/16 1 - 1-7/16
Truarc External Ret. Ring	5100 5101 5102
Anderton Internal Ret. Ring	N1300 N1301 N1302
Internal Bore Diameter	1-1/16 - 1-3/4
Industrial Internal Ret. Ring	3000-X 3001-X
Truarc Internal Ret. Ring	N5000 N5001 N5002



- Use safety goggles. Serious eye injury is possible.
- Do not use pliers with cushion grips on active electronics – there is no insulation.
- Do not use extenders or cheater bars on plier handles.
- Shield yourself and bystanders when using retaining ring pliers. Flying objects possible.
- Cut wire back in jaws – not at tip.
- Prevent exposure to excessive heat.



376L - .070 90° Tip Convertible Retaining Ring Pliers



Features and Benefits

- These Convertible Retaining Ring Pliers have a 90° tip angle
- .070 Tip size
- 7-1/8" Overall length
- Converts from internal to external or vice versa when pivot screw is moved to adjacent tapped hole
- Patented design permits quick change-over to work internal or external rings
- No screws to tighten
- Return spring reduces fatigue and facilitates operation
- Air-cushioned grips spread load across the hand increasing comfort

Product Details

Length	6-3/4"
Tip Angle (degrees)	90
Tip Size	.070
Anderton External Ret. Ring	1408 1440
Dash No. External (Internal)	-106 thru -200 (-143 thru -200) -43 thru -75 (-143 thru -200)
Industrial External Ret. Ring	4100
External Shaft Diameter	1-1/16 - 2 7/16 - 3/4
Truarc External Ret. Ring	5108 5555
Anderton Internal Ret. Ring	1308
Internal Bore Diameter	1-7/16 - 2
Industrial Internal Ret. Ring	4000
Truarc Internal Ret. Ring	5008



- Use safety goggles. Serious eye injury is possible.
- Do not use pliers with cushion grips on active electronics – there is no insulation.
- Do not use extenders or cheater bars on plier handles.
- Shield yourself and bystanders when using retaining ring pliers. Flying objects possible.
- Cut wire back in jaws – not at tip.
- Prevent exposure to excessive heat.