



5

4

3





2

1



vorverrastet
pre assembled
preassemble

strain relief verrastet
fitted
assemble



1) Markierung erster Kontakt, Ader 1 des Flachkabels
1) Contact no.1, 1st wire of flat cable
1) Contact no.1, repère 1 du câble



All Dimensions in mm
Original Size DIN A 4

Techn. Character.

Nicht tolerierte Masse/ Free size tolerances

09185145813

0,76 μm Au

09185146813

2

09185147813

3

Bestell-Nr.
Part-No.
Reference

Anforderungsstufe
performance level
Niveau de qualite

26570

01-FEB-00

JB

Mod.

Dat.

Name

HARTING EURL
F-95972 Paris



TB 0918514X813

Sub.

Blatt/ page
1/1

Detail. 01-FEB-00 Th
Insp. 01-FEB-00 JMV
Stand.
2:1

SEK 18 Female connector
14 poles
with central polarisation
without cable stop
with strain relief