



ENGLISH

## Datasheet

# Black 30m Nylon Air Hose, -40 → +80°C, Application Various

RS Stock number 3866207



### Features

Resistant to a wide range of chemicals  
Silicone free  
Abrasion resistance - excellent  
Mirror smooth inner for improved flow

Hose Inside Diameter	4mm
Hose Outside Diameter	6mm
Colour	Black
Material	Nylon
Application	Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems
Length	30m
Maximum Operating Pressure	14.5 bar
Manufacturer Series	NMSF
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+80°C