

Product Information

2474PJP125R26-28S45

EAN 4031582301649

Swivel castor with central, total or directional lock, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, wheel axle with nut, Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, with threadguards, precision ball bearing

Wheel diameter	125 mm
Width of Tread	32 mm
Bolt-Ø	28 mm
Bolt lenght	96 mm
Offset	41 mm
Swivel Interference	211 mm
Overall height	163 mm
Temperature	- 20 / + 60 °C
Standard	EN 12531
Weight	0.936 Kg / daN
Dynamic Load capacity	100 Kg / daN
Static Load capacity	200 Kg / daN



Versions:

