

Datasheet

Panel Mount

RS Stock number 464-1611



Specifications:

Rated current: 16 A

Poles: 2P+E

Hour Position: 4h

Rated Voltage: 100-130 V

Working Frequency: 50 Hz

Working Frequency: 60 Hz

Colour: Yellow

Protection Degree: IP44/IP54

Types of available outlets: Straight

Terminals: Screw

Flange: 75x75 mm

