THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



TERMINATED VIEW





1. MOLDED PARTS: UL RATED 94V-O THERMOPLASTIC, BLACK.
2. CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.
3. CONTACTS: PLATED WITH .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
   OR
   GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000015 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
4. POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSITION NUMBER 1 INDICATOR ON 10 AND 14 POSITION PRODUCT.



DETAIL Z
SCALE 10:1
TYPICAL

E	D	C	B	A	NO OF POSN	PART NUMBER
1.125	2.100	2.380	2.150	43	44	1-1658621-3
1.625	3.100	3.380	3.150	63	64	1-1658621-2
1.525	2.900	3.180	2.950	59	60	1-1658621-1
1.275	2.400	2.680	2.450	49	50	1-1658621-0
1.025	1.900	2.180	1.950	39	40	1658621-9
.875	1.600	1.880	1.650	33	34	1658621-8
.775	1.400	1.680	1.450	29	30	1658621-7
.675	1.200	1.480	1.250	25	26	1658621-6
.625	1.100	1.380	1.150	23	24	1658621-5
.525	.900	1.180	.950	19	20	1658621-4
.425	.700	.980	.750	15	16	1658621-3
.375	.600	.880	.650	13	14	1658621-2
.275	.400	.680	.450	9	10	1658621-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± 5°

MATERIAL: SEE NOTES
FINISH: SEE NOTES

DWN R. SAMICK 22AUG03
CHK C. ROHDE 22AUG03
APVD M. WALMSLEY 22AUG03
PRODUCT SPEC 108-40000
APPLICATION SPEC 114-40005
WEIGHT -

TE Connectivity

NAME
RECEPTACLE ASSY,
CENTER & MILITARY POLARIZATION,
LEAD FREE, AMP-LATCH™ NOVO

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1658621	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV C1

1658621