

Plug-in bridge - FBSRH 2-8 - 3033802

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plug-in bridge, Number of positions: 2, Color: red



Why buy this product

- The bridge has a molded extraction tool which means that it can be used conveniently and without tools for individual bridging tasks

Key commercial data

Packing unit	10 pc
GTIN	 4 046356 666916
Weight per Piece (excluding packing)	2.61 g
Custom tariff number	85389099
Country of origin	China

Technical data

Technical data

Color	red
Number of positions	2
Pitch	8.20 mm
Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141140
eCl@ss 5.1	27141140
eCl@ss 6.0	27141140
eCl@ss 7.0	27141140
eCl@ss 8.0	27141140

Plug-in bridge - FBSRH 2-8 - 3033802

Classifications

ETIM

ETIM 3.0	EC000489
ETIM 4.0	EC000489
ETIM 5.0	EC000489

UNSPSC

UNSPSC 6.01	30211829
UNSPSC 7.0901	39121426
UNSPSC 11	39121426
UNSPSC 12.01	39121426
UNSPSC 13.2	39121426