

Wear sleeves, SKF SPEEDI-SLEEVE

Shaft		Wear sleeve					Designation	US stock number	Notes
d_a		Dimensions	D	B_1	B_2	B_a			
min	max	d	$\pm 1,6$ mm $\pm 0,063$ in	$\pm 0,8$ mm $\pm 0,031$ in	$\pm 0,8$ mm $\pm 0,031$ in				
mm		mm					-	-	
84,76	85,01	84,89	94	21	25	35	CR 99333	99333	

